

# SRM Configuration Options


## SRM Rock Magnetometers

### 755-4K SRM System includes:

- 755-4K Magnetometer
- 3 measurement axes with 3DC SQUIDS
- Pulse tube cryocooler for helium free operation with 10' gas lines
- 4.2 cm room temperature through access
- Horizontal mounting stand with Ferromagnetic Shield
- Turbo Pumping Station with accessories
- Electrical package for 755R: Computer, monitor and software (see software for additional items)
- Model 520 Three axis fluxgate magnetometer
- Installation and training

### 760-4K SRM System includes:



- 755-4K Magnetometer
- 3 measurement axes with 3DC SQUIDS
- Pulse tube cryocooler for helium free operation with 10' gas lines
- 7.6 cm room temperature through access
- Horizontal mounting stand with Ferromagnetic Shield
- Turbo Pumping Station with accessories
- Electrical package for 755R: Computer, monitor and software (see software for additional items)
- Model 520 Three axis fluxgate magnetometer
- Installation and training




## SRM Software

- Computer, monitor and cables
- Software for Discrete Samples
- Software for Core and U Channels

## SRM Rock Degausser & Magnetizer




## SRM Rock Magnetometers - Sample Handler



## SRM Accessories

- Turbo Pump
- Susceptibility Meter
- Fluxgate Magnetometers

## SRM Parts and Supplies



## SRM Parts and Supplies

