

SRM Configuration Options

SRM Rock Magnetometers

755-4K SRM System includes:

- 755-4K Magnetometer
- 3 measurement axes with 3DC SQUIDS
- Pulse tube cryocooler for helium free operation with 10' gas lines
- 4.2 cm room temperature through access
- Horizontal mounting stand with Ferromagnetic Shield
- Turbo Pumping Station with accessories
- Electrical package for 755R: Computer, monitor and software (see software for additional items)
- Model 520 Three axis fluxgate magnetometer
- Installation and training

760-4K SRM System includes:


- 755-4K Magnetometer
- 3 measurement axes with 3DC SQUIDS
- Pulse tube cryocooler for helium free operation with 10' gas lines
- 7.6 cm room temperature through access
- Horizontal mounting stand with Ferromagnetic Shield
- Turbo Pumping Station with accessories
- Electrical package for 755R: Computer, monitor and software (see software for additional items)
- Model 520 Three axis fluxgate magnetometer
- Installation and training




SRM Software

- Computer, monitor and cables
- Software for Discrete Samples
- Software for Core and U Channels

SRM Rock Degausser & Magnetizer




SRM Rock Magnetometers - Sample Handler



SRM Accessories

- Turbo Pump
- Susceptibility Meter
- Fluxgate Magnetometers

SRM Parts and Supplies



Extra Sampler Handler Parts

- | | |
|---------------------------------|--------------------------|
| Tray, 99-Position, 2CM | Discrete Sample Boats |
| Tray, 99-Position | Motor Drive |
| Fiberglass Sample Tray | Modify for Stepper Motor |
| Mylar Sample Tray | Custom Tray |
| Mylar Sample Tubes 1 meter long | Drive Belt |

